

VARIOVAC

semi-automatic tray sealer
with turntable

Rotarius VG

vacuum / gas

gas flushing

impulse vacuum

sealing



- higher productivity in comparison to the conventional drawer-type tray sealer
- O₂ security device inclusive
- continuous working process without standby time
- simple changing of format dies
- small footprint
- perfect product presentation

know-how
in
packaging

Rotarius VG

Great flexibility is given due to the fact, that the **Rotarius VG** seals trays made from all kind of different material (PP, PET, PS, aluminium and laminated carton). The chosen lidding film must correspond to the characteristics of the trays.

For better product presentation you can also use **printed lidding film** on the **Rotarius VG**.

Changing from one tray size to another is done easily and **without any tools**.


The manual turntable enables high efficiency: whilst the exchange of atmosphere is made in the sealing-/cutting station, the sealed and contour cut trays can be unloaded and new filled trays placed into the loading/unloading station. Residual film will be automatically coiled and removed.

Options: liquid separator, particle filter, photoelectric code control for printed film

max tray sizes in mm;
max. height 100 mm




406 x 294




406 x 137




190 x 294




406 x 82




118 x 294




190 x 137




82 x 294



190 x 82



118 x 137



IP 65 rated
subject to technical alterations
Made in Germany

Technical Data:

control:	Siemens S 7, handling via touch screen
electr. connection:	3L/N/PE, 400 V/50 Hz, max. 7 kW
compressed air:	6 bar / 28 Ltrs per min.
cycles:	4 – 8 cycles/min., depending on tray size
vacuum pump:	vacuum/gas/seal BUSCH 63 m ³ /h, integrated (opt. 100 m ³ /h)
pneumatic:	Festo / Univer
film diameter:	max. 300 mm
weight:	approx. 450 kgs.
space required:	1,6 m ²



VARIOVAC

VARIOVAC PS SystemPack GmbH

Ernst-Litfass-Str. 3 und 5
D-19246 Zarrentin am Schaalsee
Tel: +49-38851-823-0
Fax: +49-38851-823-220
www.variovac.de